

## MODEL COMPARISON CHART

MODEL N O.	ELECTRIC BIDET				FAR INFRARED RAY BIDET		
	 PB-X6500	 PB-X5500	 PB-X2500	 PB-X800	 XB-U5700	 XB-U3000B	
	NOZZLE	TWIN	TWIN	TWIN	TWIN	TWIN	
	FAR INFRARED RAY NOZZLE	-	-	-	-	✓	
	STAINLESS NOZZLE	optional	optional	optional	optional	optional	
CLEANSING	WARM WATER	✓	✓	✓	✓	✓	
	ANTERIOR/FEMININE	✓	✓	✓	✓	✓	
	POSTERIOR/FAMILY	✓	✓	✓	✓	✓	
	SELF CLEAN	✓	✓	✓	✓	✓	
	ENEMA / MASSAGE	✓	✓	✓	-	✓	
	WIDE WASH	✓	-	-	-	✓	
	CHILD WASH	✓	✓	-	-	✓	
		SEAT TEMPERATURE	✓	✓	✓	✓	✓
		WATER TEMPERATURE	✓	✓	✓	✓	✓
CONTROL	WARM AIR TEMPERATURE	✓	✓	✓	Optional	✓	
	WATER PRESSURE	✓	✓	✓	✓	✓	
	NOZZLE POSITION	✓	✓	✓	✓	✓	
SAFETY	ELECTRIC CIRCUIT BREAKER	optional	optional	optional	optional	optional	
	SEAT SENSOR	✓	✓	✓	Optional	✓	
	ANTI-BACTERIAL	✓	✓	✓	✓	✓	
CONVENIENT	WIRELESS REMOTE	✓	-	-	-	-	
	CONTROL PANEL	-	✓	✓	✓	✓	
	ENERGY SAVING	✓	✓	✓	-	✓	
	SOFT CLOSE	✓	✓	✓	✓	✓	
SANITATION	DEODORIZER	optional	✓	✓	-	✓	
	WATER PURIFIER	✓	✓	✓	-	✓	
COLOR	WHITE & RED	✓	✓			✓	
	WHITE & BLACK		✓			✓	
	WHITE	✓		✓	✓	✓	
Others	N/W, G/W	5kg / 7 kg	5kg / 7 kg	5kg / 7 kg	5kg / 7 kg	5kg / 7 kg	
	Dim. (W x L x H)	550 x 565 x 150	476 x 535 x 150	483 x 530 x 137	483 x 530 x 137	476 x 535 x 150	
	Packing (W x L x H)	602 x 542 x 202	588 x 542 x 202	602 x 542 x 202	602 x 542 x 202	588 x 542 x 202	



High technological functions will upgrade quality of your life.



# FAR INFRARED RAY SAFE STERILIZATION

## Features of Far-Infrared Ray Nozzle



### Effect of Far Infrared ray

Has the ability to penetrate, refract, radiate & reflect. The human body can absorb FIR because of its deep penetrating ability. When FIR penetrates through the skin to the subcutaneous tissues, it transforms from light energy into heat energy.

The thermal effect within the deep layers of tissues cause blood vessels in capillaries to dilate, promoting better blood circulation, and the heat produced helps to get rid of body toxins and metabolic wastes through sweating.

### Why Far-Infrared Ray Nozzle?

- Bacteria on Nozzle tip of wash / bidet to be sterilized by 99.9% by Far Infrared Ray Heater for cleaning & securing washing of nozzle.
- The nozzle with Far Infrared Ray enable to promote metabolic by Far Infrared ray during use of Bidet.

### How To Operate?

1. When seated Far-Infrared rays heater begins to work to sterilize nozzle tip.
2. When wash/bidet is operated, Far-Infrared rays come in contact with body improves human health system
3. After wash/bidet is operated, as self nozzle cleaning process, Far-Infrared rays sterilize nozzle tip for 10 minutes.

### Test results of Far Infrared ray's sterilization



Tested by	Type of Bacteria				
	E. Coli	Stacpch uysloco	S. typhimurium	S. flexneri	P. aeruginosa
KRICT Reg.no.: 20069-TBH-000565	-	-	99.9%	86.7%	94%
KIDA Reg.no.: KFIA-140	99.9%	99.9%	-	-	-

### Test results of Far Infrared ray

Tested by	Emissivity(5-20um)	Radiation Energy (W/m2.um, 150°C)
KIDA Reg.no.: KFIA-140	Tested by	Tested by

PASECO Bidet aims to make 99.9% sterilizable antibacterial bidet for clean & healthy use by Far-Infrared ray, anti-bacterial nozzle, anti-bacterial seat that PASECO's cutting-edge technology enable perfect sterilization system.

## ELECTRIC BIDET

### PB-X6500



- Convenient Remote Control
- Energy Saving
- Instant Warm Water / Warm Air Dryer
- Adjustable Seat/water temp
- Adjustable water pressure
- Enema / Massage Wash
- Wide / Child Wash
- Water Purifier / Seat Sensor
- Optional
  - Stainless Nozzle
  - Electric Circuit Breaker
  - Powerful Deodorizer (Carbon Filter)

### PB-X5500



- Energy Saving
- Warm Water / Warm Air Dryer
- Powerful Deodorizer (Carbon Filter)
- Adjustable Seat/water temp
- Adjustable water pressure
- Enema / Massage Wash
- Auto Wash / Child Wash
- Seat Sensor / Water Purifier
- Optional
  - Stainless Nozzle
  - Electric Circuit Breaker

### PB-X2500



- Energy Saving
- Warm Water / Warm Air Dryer
- Powerful Deodorizer (Carbon Filter)
- Adjustable Seat/water temp
- Adjustable water pressure
- Massage / Auto Wash
- Seat Sensor / Water Purifier
- Optional
  - Stainless Nozzle
  - Electric Circuit Breaker

### PB-X800



- Warm Water
- Adjustable Seat/water temp
- Adjustable water pressure
- Optional
  - Stainless Nozzle
  - Warm Air Dryer
  - Seat Sensor

## PATENT FAR INFRARED RAY BIDET

### XB-U5700

- Far Infrared Ray Nozzle
- Energy Saving
- Powerful Deodorizer (Carbon Filter)
- Warm Water / Warm Air Dryer
- Adjustable Seat/water temp
- Adjustable water pressure
- Enema / Massage Wash
- Auto Wash / Child Wash
- Water Purifier / Seat Sensor



### XB-U3000

- Far Infrared Ray Nozzle
- Energy Saving
- Warm Water / Warm Air Dryer
- Powerful Deodorizer (Carbon Filter)
- Adjustable Seat/water temp
- Adjustable water pressure
- Massage Was / Auto Wash
- Seat Sensor / Water Purifier



**FAR INFRARED RAY STERILIZATION**  
Killing 99.9% of bacteria from nozzle

**POWERFUL DEODORIZER**

**HOT WATER NOZZLE STERILIZATION**  
Additional for perfect killing bacteria

**SEAT SENSOR**

**POWER SAVING**

**WATER PURIFIER**

## ELECTRIC BIDET

### PWS-600



- Power Saving
- Heated Seat
- Adjustable Seat Temp
- Easy Installation
- Power on/off
- Seat Sensor
- Dim.(mm): 550(W)x565(L)x150(H)



### PNB-300

- Cold & Hot water wash
- Ad justable water
- Pressure(3 steps)
- Nossle self-cleaning
- Ad justable temperature



### PNB-20

- Cold & Hot water wash
- Ad justable water
- Pressure(3 steps)
- Nossle self-cleaning
- Ad justable temperature



### PNB-100

- Cold water wash only
- Adjustable water



**NOZZLE SELF-CLEANING**  
Warm water washing during 1 min after use to clean nozzles



**SOFT CLOSE**  
Prevent seat cover damage



**POWER SAVING**



**WIDE WASH**



**TWIN NOZZLE**



**REMOTE CONTROLLER**



**HEATED SEAT**



**ADJUSTABLE NOZZLE POSITION**